



### Transmission Curve

Range: 350 - 1050 nm  
 Thickness:  $2.02 \pm 0.01$   
 Serial number: 2458365

Resolution: 1.2 nm  
 Precision: 0.01 %

### Filter Constrast Booster - Baader

Oriel Cornerstone 260 + Oriel 20 W  
 Angle:  $0^\circ$  Steps: 1 nm  
 Tester: Carlos Eugenio Tapia Ayuga

LICA - UCM  
 Date: 22 - 03 - 2012  
<http://guaix.fis.ucm.es/lica>

